Fast HF measurements.

Anywhere.





Hydrogen Fluoride Analyzer (HF, H₂O)

Features and Benefits

- Fastest response: 1-Hz continuous measurements allow observation of transient and time varying flows
- Measures a wide range of concentrations
- High-resolution absorption spectra always viewable
- Low power: ideal for field applications
- New Enhanced Performance model provides ultra-low drift and unsurpassed precision

LGR's Hydrogen Fluoride Analyzer (HFA) provides sensitive measurements of HF in ambient air or in industrial process flows with extremely high precision and sensitivity. No longer do you have to spend a lot of money or wait a long time to measure hydrogen fluoride gas with high sensitivity – LGR's Hydrogen Fluoride Analyzer provides measurements every second with ppb-level precision. In addition, the HFA can report measurements quickly over a very wide range of HF concentrations.

LGR's HFA is available in different packages to allow users to select the one most suitable for their needs. LGR's standard LGR's rackmount package fits in a standard instrumentation rack and requires an external keyboard, mouse, and video monitor. For highest performance, the HF Analyzer is now available in LGR's "Enhanced Performance" (or EP) package. The EP version incorporates proprietary internal thermal control for ultra-stable measurements with unsurpassed precision, accuracy and drift. LGR's analyzers provide reliable *guaranteed* measurements at mole fractions more than 20 times ambient levels. In addition, a suite of options and accessories expands the usability for just about any application.

The HFA uses LGR's patented Off-axis ICOS technology, a fourth-generation cavity enhanced absorption technique. Off-axis ICOS has many advantages over conventional cavity ringdown spectroscopy (CRDS) techniques such as being alignment insensitive, having a much shorter measurement time, and not requiring expensive and power consuming auxiliary components.

As with all LGR instruments, the HFA includes an internal computer (Linux OS) that can store data practically indefinitely on its internal hard drive (for long-term operation), and that can send real-time data to a data logger through its analog, digital and Ethernet outputs. Furthermore, the HFA may be controlled remotely via the Internet. This capability allows the user to easily and fully control the analyzer simply using a web browser.

Hydrogen Fluoride Analyzer (HF, H₂O)

Performance Specifications

Repeatability / Precision (1-sigma): HF: <0.1 ppb (1 sec), <0.07 ppb (10 sec), <0.05 ppb (100 sec)

Response Time (flow time through meas. cell): 10 s (with standard internal pump),

<2 s (with optional external N920 vacuum pump)

Measurement Range: HF: 0.2 – 2000 ppb

Operational Range: HF: 0 – 30 ppm H₂O: 10 – 20000 ppm (non-condensing)

Outputs: Digital (RS232), Analog, Ethernet, USB

Data Storage: Internal Hard Disk Drive (optional Solid State Drive)

Ambient Humidity:

0 - 100%

Operating Temperature: $5 - 45 \degree C$ $0 - 50 \degree C$

Inlet / Outlet Fittings: 1/4", 3/8", and 1/2" Swagelok®

Power Requirements:

115/230 VAC, 50/60 Hz 100 W (Standard Model) 300 W (Enhanced Performance)

Dimensions:

8.75" H x 19" W x 24" D (Standard Model) 15.75" H x 19" W x 24" D (Enhanced Performance)

Weight:

29 kg (Standard Model) 40 kg (Enhanced Performance)



Ordering Information

907-0017: Rackmount Package 911-0017: Enhanced Performance Package

Accessories

908-0003-9001: Multiport Inlet Unit – 16-inlet port multiplexer 908-0003-9002: Multiport Inlet Unit – 8-inlet port multiplexer

908-0008-9009: N920 Pump

904-0002: Data Logging System – multi-channel data logging system records and synchronizes serial (RS-232) outputs from multiple LGR analyzers and other devices (GPS, anemometers)



L G R Los Gatos Research

Los Gatos Research, Inc. 67 East Evelyn Avenue, Suite 3 Mountain View, CA 94041-1529 Phone: +1 650–965–7772 Fax: +1 650–965–7074 Sales: sales@lgrinc.com

www.lgrinc.com